






- 1.0 GENERAL NOTES  
 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]  
 1.2 FOR PATENT INFO: <https://www.cs-pat.com>  
 2.0 DESIGN NOTES  
 3.0 MANUFACTURING/SPECIAL REQUIREMENTS  
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.  
 3.2 BAR GRATING ALIGNED ACROSS CENTER CHANNELS.  
 4.0 TEST  
 5.0 PACKAGING  
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005  
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER  
 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED  
 5.4 UP TO 5% ADDITIONAL HARDWARE INCLUDED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	ACG 13FEB03	TP
G	REPLACE SQUARE WASHERS WITH FLAT WASHERS	AW 21JUN07	TP
H	ADD PLAN VIEWS UPDATE WEIGHTS	MSM 05APR12	TP
J	MTC7902081001 WAS MTC79021010.07	RJC 13APR17	TP
K	UPDATED DRAWING FORMAT; MTC390324 AND TS1220 WAS GCM03	LL1090 08MAR24	BCROSS 40190172CMO



DETAIL A  
SCALE 1 : 6



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;  
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	MTC7902101001	SIDE CHANNEL C8 X 11.5#	2	113.50 LBS	
2	MTC7902101002	10' CENTER CHANNEL	4	108.98 LBS	
3	MTC7902081001	24" X 120" BAR GRATING	5	141.45 LBS	
4	MTC790203	CHANNEL ADAPTER ANGLE	8	7.07 LBS	
5	GB-05205	5/8" X 2" GALV BOLT KIT	32	0.26 LBS	
6	GWF-05	5/8" GALV FLAT WASHER, 1.70D	64	0.06 LBS	
7	MTC390324	BAR GRATING CLIP	30	0.17 LBS	
8	TS1220	12-24 X 2" SELF DRILLING SCREW	30	0.03 LBS	

DENSITY		lbs/in <sup>3</sup>
MASS	1448.02	lbs
VOLUME	5138.60	in <sup>3</sup>
SURFACE AREA	51521.00	in <sup>2</sup>
HEIGHT	9.0"	
LENGTH	120.0"	
WIDTH	120.0"	

© 2024 CommScope, Inc. Confidential

HIDE BAR GRATING FOR CLARITY

**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER							
1 PLACE .X[X] ± 0.12[3.0]	3 PLACE .XXX[X] ± 0.03[0.8]	<b>EQ-P1010-B</b>							
2 PLACE .XX[X] ± 0.06[1.5]	ANGLES ± 2°								
FINISH		MATERIAL							
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994		TITLE							
CE	ACG	13FEB03	<b>10' X 10' EQUIPMENT PLATFORM BASE</b>						
RW	LL1090	03/14/2024							
AD	YW1045	03/18/2024							
RE	YMENG	04/02/2024							
ECN 40190172CMO		SCALE	DOCUMENT NO.						
		<b>1:32</b>	<b>EQ-P1010-B</b>						
SIZE	Auth Group	INSL	MODEL						
<b>C</b>			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	SHEET
			03	RE	M	01	RE	K	1 OF 1