

ConQuest® Empty Conduit, 2 in, SCH 40, ribbed, orange, with pull tape



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Empty conduit
Product Brand	ConQuest®
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Color	Orange
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Ribbed

Dimensions

Length	762 m 2500 ft
Inner Diameter, nominal	51.994 mm 2.047 in
Outer Diameter, nominal	60.325 mm 2.375 in
Wall Thickness Designation	SCH 40
Wall Thickness, minimum	3.912 mm 0.154 in
Nominal Size	2 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
----------------------------------	---------------------------------------

CX3799686 | 2000040 RIB WP1250TAPE COEX

Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE) Polyester
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	660.4 mm 26 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Breaking Strength	566.99 kg 1250 lb
Pull Line Type	Tape
Pulling Tension, maximum	1,043.262 kg 2300 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	729.2 kg/km 490 lb/kft
--------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance