

CTR 1204 January 4, 2023 Commscope.com

### **Customer Test Report on NOVUX™ SEC-100 aerial wall**

#### terminal

This test report details the results of optical, mechanical, and environmental tests carried out on NOVUX<sup>TM</sup> SEC-100 aerial wall terminal.

Testing is done according to:

- RUD 5580 C – Performance specification of NOVUX SEC-100 aerial wall terminal and cable clip

An overview table gives summarized results. Detailed test results and sample descriptions are described further in this document.

#### Conclusions

All performed tests were done according to the above-mentioned specification and were completed with positive results

The product is designed to operate in outdoor, aerial, non-weather protected locations as described in the following standards:

- ETSI EN 300 019-2-4 T4.1 Stationary use at non-weather protected locations
- IEC 61753-1 Category A free breathing terminal



CTR 1204 January 4, 2023 Commscope.com

#### Content

1 Test results overview		4	
1.1 Overview sealing performance results	4		
1.2 Overview optical performance results	4		
1.3 Overview material performance results	4		
1.4 Overview storage and transportation performance results	4		
2 Sealing performance pass / fail criteria		5	
2.1 Protection against ingress of dust IP5x	5		
2.2 Protection against ingress of water IPx5	6		
2.3 Visual examination	7		
3 Detailed test results for sealing performance		8	
3.1 Assembly/disassembly of terminal	8		
3.2 Cable retention for terminal	8		
3.3 Cable bending (only drop cables of terminal)	9		
3.4 Cable torsion (only drop cables of terminal)	9		
3.5 Impact of terminal	10		
3.6 Change of temperature for terminal	10		
3.7 Salt mist for terminal	11		
4 Optical performance pass / fail criteria		12	
4.1 Change in attenuation (for climatic test)	12		
4.2 Transient loss (for mechanical tests)	13		
4.3 Visual examination	14		
5 Detailed test results for optical performance		15	
5.1 Cable retention	15		
5.2 Cable bending	15		
5.3 Cable torsion	16		
5.4 Reconfiguration 1	16		
5.5 Reconfiguration 2	17		
5.6 Shock	17		
5.7 Vibration	18		
5.8 Change of temperature	18		



CTR 1204 January 4, 2023 Commscope.com

6 Detailed test results for material performance		19
6.1 Resistance to solvents and contaminating fluids	19	
6.2 UV resistance of outer polymeric materials	19	
6.3 Fungus resistance (Mold growth)	20	
7 Detailed test results for storage and transport performance		21
7.1 Cold	21	
7.2 Dry heat	21	
7.3 Damp heat (steady state)	22	
8 Test sample description		23
8.1 Sealing performance test samples	23	
8.2 Optical performance test samples	24	
9 Test set-ups		26
9.1 Sealing performance testing	26	
9.2 Optical performance testing	28	
9.3 Storage and transport test set up	31	
10 Equipment and calibration		33
11 Trade-marks		34
12 Contact information		35



CTR 1204 January 4, 2023 Commscope.com

#### 1 Test results overview

Detailed results are given further in section 2 - 7.

#### 1.1 Overview sealing performance results

Section	Test Name	Number of samples	Result
3.1	Assembly / disassembly closures	4	Pass
3.2	Cable retention wall terminal box	4	Pass
3.3	Cable bending	4	Pass
3.4	Cable torsion	4	Pass
3.5	Impact	8	Pass
3.6	Change of temperature wall terminal	4	Pass
3.7	Salt mist	4	Pass

#### 1.2 Overview optical performance results

Section	Test Name	Number of samples	Result
5.1	Cable retention	1	Pass
5.2	Cable bending	1	Pass
5.3	Cable torsion	1	Pass
5.4	Reconfiguration 1	2	Pass
5.5	Reconfiguration 2	2	Pass
5.6	Shock	2	Pass
5.7	Vibration	2	Pass
5.8	Change of temperature	2	Pass

#### 1.3 Overview material performance results

Section	Test Name	Number of samples	Result
6.1	Resistance to solvents and	6 samples black	Pass
	contaminating fluids	6 samples grey	Pass
6.2	UV resistance of outer polymer	3 samples black	Pass
	materials	3 samples grey	Pass
6.3	Fungus resistance (Mold growth)	4 samples black	Pass
		4 samples grey	Pass

#### 1.4 Overview storage and transportation performance results

Section	Test Name	Number of samples	Result
7.1	Cold	4	Pass
7.2	Dry heat	4	Pass
7.3	Damp heat (steady state)	4	Pass



CTR 1204 January 4, 2023 Commscope.com

#### 2 Sealing performance pass / fail criteria

#### 2.1 Protection against ingress of dust IP5x

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condi	tions	Test standards followed	Requirements
Dust type: Dust density: Pressure: Duration:	Talcum powder 2 kg/m³ No pressure differences 8 h	IEC 60529	Ingress of dust in the terminal shall not cause functional problems like preventing access to or handling of fibers and components, impossible to clean connectors and adapters. The IP5x requirements is not required for the cable protection clip.

Number of samples: See test samples of tests in sections 3	Pass	
--	------	--



CTR 1204 January 4, 2023 Commscope.com

#### 2.2 Protection against ingress of water IPx5

#### General

Product	NOVUX™ SEC 100 aerial wall terminal	
Date of testing	November 2022	

Method and conditions		Test standards followed	Requirements
Spray medium:	Tap water at ambient temperature	IEC 60529	Water sprays against the terminal from any practicable
Internal Ø nozzle:	6.3 mm		direction shall not cause
Flow rate:	12.5 l/minute ± 5%		accumulation of water exceeding
Water pressure:	Adjusted to get specified flow rate		1% of the inner volume of the terminal.
Core of water stream:	Diameter 40 mm at 2.5 m distance.		No ingress of water allowed in the cable protection clip.
Distance nozzle/			'
sample:	Between 2.5 m and 3 m		
Sample position:	Wall mounted in a position according to the installation instructions, 1.5 meters above ground.		
Locations:	All practicable accessible sides:		
Duration:	1 minute / m2 of the terminal surface, but in total at least 3 minutes		
	1 minute on cable protection		
	clip		

	Number of samples:	See test samples of tests in sections 3.	Pass	
--	--------------------	--	------	--



CTR 1204 January 4, 2023 Commscope.com

#### 2.3 Visual examination

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Examination of product with naked eye.	Inspection with the naked eye for flaws, defects, permanent deformation, cracks, or impurities that could impair functionality.	IEC 61300-3-1	No defects which would adversely affect product performance

Number of samples:	See test samples of tests in sections 3.	Pass	
ramber of samples.	see test samples of tests in sections s.	1 433	

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 3 Detailed test results for sealing performance

#### 3.1 Assembly/disassembly of terminal

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Number re-entries:	5 times	IEC 61300-2-33	Visual examination (see 2.3)
Aging between each			Protection against ingress of
re-entry:	At least one temperature cycle		dust (IP5x) (see 2.1)
Temperature cycle:	(-40 ±2) °C to (+65±2) °C		Protection against ingress of
Dwell time:	4 h		water (IPx5) (see 2.2)
Transition:	1 °C/minute		No dust test required for clip

#### Results

#### 3.2 Cable retention for terminal

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	ns	Test method followed	Requirements
Test temperatures:	(-15 ± 2) °C and (+45 ± 2) °C	IEC 61300-2-4	Visual examination (See 2.3)
Force:	Ø cable (mm) x 10 N/mm for feeder		Protection against ingress of
	cables		dust (IP5x) (see 2.1)
	25 N for drop cables		Protection against ingress of
Rate:	Load smoothly, applied in 15 s		water (IPx5) (see 2.2)
Duration:	Feeder cable: 1 h		
	Drop cable: 1 minute		

Number of samples:	4	Pass

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 3.3 Cable bending (only drop cables of terminal)

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Test temperatures: Bending angle:	(-15 ± 2) °C and (+45 ± 2) °C -30° and +30° in random direction	IEC 61300-2-37	Visual examination (see 2.3) Protection against ingress of dust (IP5x) (see 2.1)
Duration at each extreme position: Point of application: Number of cycles:	5 minutes 400 mm from end of cable seal 5 cycles per cable and per test temperature in random directions, unless not possible by physical constraints or cable design.		Protection against ingress of water (IPx5) (see 2.2)

#### Results

Number of samples: 4	Pass	
----------------------	------	--

#### 3.4 Cable torsion (only drop cables of terminal)

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Test temperature:	(-15 ± 2) °C and (+45 ± 2) °C	IEC 61300-2-5	Visual examination (See 2.3)
Torsion angle:	- 90° and +90°		Protection against ingress of
Point of application:	400 mm from end of cable seal		dust (IP5x) (see 2.1)
Duration at each			Protection against ingress of
extreme position:	5 minutes		water (IPx5) (see 2.2)
Tensile load:	None		
Number of cycles:	5 per cable per test temperature		

Number of Samples. 4 Pass
---------------------------



CTR 1204 January 4, 2023 Commscope.com

#### 3.5 Impact of terminal

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and conditions	S	Test method followed	Requirements
Test temperatures:	(-15 ± 2) °C and (+45 ± 2) °C	IEC 61300-2-12	Visual examination (see 2.3)
Impact tool:	Steel ball	Method B	Protection against ingress of
Mass:	1 kg		dust (IP5x) (see 2.1)
Drop height:	0.2 m		Protection against ingress of
Location:	In the middle on front side		water (IPx5) (see 2.2)
Number of impacts	1		

#### Results

Number of samples:	16	Pass
rannoci di sampics.	10	1 433

#### 3.6 Change of temperature for terminal

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and conditions	5	Test method followed	Requirements
Lowest temperature:	(-40 ± 2) °C	IEC 61300-2-22	Visual examination (see 2.3)
Highest temperature:	(+65 ± 2)°C		Protection against ingress of
Dwell time:	4 h		dust (IP5x) (see 2.1)
Transition:	1°C / minute		Protection against ingress of
Number of cycles:	12		water (IPx5) (see 2.2)

Number of samples:	4	Pass



CTR 1204 January 4, 2023 Commscope.com

#### 3.7 Salt mist for terminal

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condit	tions	Test method followed	Requirements
Temperature: Salt solution:	$(+35 \pm 2)$ °C 5 % NaCl in water (pH between 6,5 and 7,2)	IEC 61300-2-26	Visual examination (see 2.3) no corrosion of metal parts, color change due to
Duration: Test sample	5 days Closed box		passivation is allowed.

Number of samples: 4	Pass
----------------------	------



CTR 1204 January 4, 2023 Commscope.com

#### 4 Optical performance pass / fail criteria

#### 4.1 Change in attenuation (for climatic test)

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal	
Date of testing	July 2022	

Method and conditions		Test method followed	Requirements	
Source wavelength: Sampling period:	1310 nm, 1550 nm and 1625 nm At least every 10 minutes	IEC 61300-3-3	For each incoming fiber (Note 1): Splice only: $\delta \leq 0.2$ dB during test $\delta \leq 0.1$ dB after test Splice and patch (1 connection): $\delta \leq 0.3$ dB during test $\delta \leq 0.2$ dB after test If other passive optical components are part of the optical path, the abovementioned change in attenuation values should be increased with the maximum allowed change in attenuation value specified during and after test for this passive optical component. For wavelength selective components the test wavelength might have to be changed to the operating wavelength(s) of the component(s). For example: Splice, 1x4 splitter and patch (1 connection): $\delta \leq 0.6$ dB during test $\delta \leq 0.5$ dB after test	

#### Notes:

- The change in attenuation  $\delta$  refers to the  $\pm$  deviation from the original value of the transmitted power at the start of the test and are based on the use of ITU-T G.657 fibers.
- An "incoming fiber" is defined as a part of an optical circuit containing the fiber entering the product, spliced, or connected to a fiber leaving the product.
- An optical circuit contains several (typically 10, unless fewer fibers are available) live "incoming fibers". Light will sequentially flow through all the "incoming fibers" by "daisy chaining" the live incoming fibers.

Number of samples:	See test samples of tests in sections 5.	Pass	



CTR 1204 January 4, 2023 Commscope.com

#### 4.2 Transient loss (for mechanical tests)

#### General

Product	NOVUX™ SEC 100 aerial wall terminal	
Date of testing	July 2022	

Method and conditions		Test method followed	Requirements	
Source wavelength: Sampling period:	1550 nm and 1625 nm At least 0.25 ms	IEC 61300-3-28	For each circuit with live incoming fibers $\delta \leq 0.5$ dB during test $\delta \leq 0.1$ dB after test (for splice only) $\delta \leq 0.2$ dB after test (for splice and patch) $\delta \leq 0.3$ dB after test (for connectorized splitter)	

#### Notes:

- The change in attenuation  $\delta$  refers to the +/- deviation from the original value of the transmitter power at the start of the test and are based on the use of ITU-T G.657 fibers
- An "incoming fiber" is defined as a part of an optical circuit containing the fiber entering the product, spliced, or connected to a fiber leaving the product.
- An optical circuit contains several (typical 10 unless fewer fibers are available) live "incoming fibers". Light will sequentially flow through all the "incoming fibers" by "daisy chaining" the live incoming fibers.

Number of samples:	See test samples of tests in sections 5.	Pass	
--------------------	--	------	--



CTR 1204 January 4, 2023 Commscope.com

#### 4.3 Visual examination

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	July 2022

Method and condition	s	Test method followed	Requirements
Examination of product with naked eye.	Inspection with the naked eye for flaws, defects, cracks, or impurities that could impair functionality.	IEC 61300-3-1	No defects which would adversely affect product performance

Number of samples: See test samples of tests in sections 5.	Pass	
---	------	--

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

### 5 Detailed test results for optical performance

#### 5.1 Cable retention

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	ns	Test method followed	Requirements
Test temperature:	(+23 ± 5) °C	IEC 61300-2-4	Visual examination (see 4.3)
Force:	Øcable (mm) x 10 N/mm for		Transient loss (see 4.2)
	feeder cable		
	25 N for drop cable		
Rate:	Load smoothly applied in 15 s		
Duration:	Feeder cable: 1 h		
	Drop cable: 1 minute		

#### Results

N		
Number of samples: 1	Pass	

#### 5.2 Cable bending

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Test temperature:	(+23 ± 5) °C	IEC 61300-2-37	Visual examination (see 4.3)
Bending angles:	From 0° to - 90° to +90° to 0°		Transient loss (see 4.2)
	(= 1 cycle)		
Duration at each			
extreme position:	5 minutes		
Point of application:	400 mm from end of cable seal		
Number of cycles:	5 cycles per cable in random		
	directions, unless not possible		
	by physical constraints or cable		
	design.		

Number of samples: 1 Pass
---------------------------



CTR 1204 January 4, 2023 Commscope.com

#### 5.3 Cable torsion

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and conditions		Test method followed	Requirements
Test temperature:	(+23 ± 5) °C	IEC 61300-2-5	Visual examination (see 4.3)
Torsion angle:	From 0° to - 90° to +90° to 0° (= 1 cycle)		Transient loss (see 4.2)
Point of application: Duration at each	400 mm from end of seal		
extreme position:	5 min		
Tensile load:	none		
Number of cycles:	5 per cable		

#### Results

Number of samples:	1	Pass
--------------------	---	------

#### 5.4 Reconfiguration 1

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	September 2022

Method and conditions		Test method followed	Requirements
Following handling operations are done on the terminal:	1. Open terminal and get access to fiber management system 2. Hinge all trays between extreme positions 3. Secure fiber management system and close box 4. Repeat steps 1 to 3 for at least 50x	IEC 61300-2-33	Visual examination (see 4.3) Transient loss (see 4.2)

Number of samples: 2 Pass	Number of samples: 2	
---------------------------	----------------------	--



CTR 1204 January 4, 2023 Commscope.com

#### 5.5 Reconfiguration 2

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	s	Test method followed	Requirements
Following handling operations are done on the terminal:	<ol> <li>Open terminal and get access to fiber management system</li> <li>Open cable clip, cut nonactive fiber bundle, pull back into terminal and close cable clip</li> <li>Add new drop cable and splice/connect it.</li> <li>Secure fiber management system and close box</li> </ol>	IEC 61300-2-33	Transient loss after test in active circuit (see 4.2)

#### Results

Number of samples:	2	Pass
radified of samples.	<u>_</u>	1 433

#### 5.6 Shock

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	September 2022

Method and conditio	ns	Test method followed	Requirements
Wave form:	Half sine	IEC 61300-2-9	Visual examination (4.3)
Acceleration:	150 m/s <sup>2</sup>		Transient loss (see 4.2)
Duration:	11 milliseconds		
Number of shocks:	In total 18 shocks		
Axes:	3 shocks per direction of each		
	axis		
	3 mutually perpendicular		

	Number of samples:	2	Pass
--	--------------------	---	------



CTR 1204 January 4, 2023 Commscope.com

#### 5.7 Vibration

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal	
Date of testing	September 2022	

Method and condition	ns	Test method followed	Requirements
Sweep range:	From 5 Hz to 500 Hz to 5 Hz (=	IEC 61300-2-1	Visual examination (see 4.3)
	1 cycle)		Transient loss (see 4.2)
Frequency change:	1 octave/minute		
Crossover freq.:	9 Hz		
- below 9 Hz:	Amplitude 3.5 mm		
- above 9 Hz:	10 m/s² (~ 1 g)		
Axes:	3 mutually perpendicular		
Duration:	10 cycles/axis		

#### Results

Number of samples: 2	Pass
----------------------	------

#### 5.8 Change of temperature

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and condition	S	Test method followed	Requirements
Lowest temperature: Highest temperature: Dwell time: Transition time:	(-40 ± 2)°C (+65 ± 2)°C 4 h 1 °C / minute	IEC 61300-2-22	Visual examination (see 4.3) Change in attenuation for climatic test (see 4.1)
Number of cycles:	12		

Number of samples: 2	Pass
----------------------	------

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 6 Detailed test results for material performance

#### 6.1 Resistance to solvents and contaminating fluids

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	January 2016

Method and condition	ns	Test method followed	Requirements
Test temperature:	(+23 ± 5) °C	IEC 61300-2-34	Visual examination (see 2.3)
Media:	pH2 (HCL) pH12 (NaOH)		No swelling, no cracking of polymer materials
Test time:	5 days		

#### Results

Number of samples:	6 samples Black	Pass	
	6 samples Grey	Pass	

#### 6.2 UV resistance of outer polymeric materials

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	February 2016

Method and condition	ns	Test method followed	Requirements
UV source:	Lamp type 1A Fluorescent	ISO 4892-3	Visual examination (see 2.3)
	lamps (UVA 340 nm)	ASTM G.154	
Exposure cycles:	Cycle 1: Alternating UV and		Reduction in mechanical
	condensation cycle		properties (tensile strength and
UV:	8 h at (+60 $\pm$ 3) °C, UV-light		elongation at yield) shall be less
Condensation:	4 h at (+50 $\pm$ 3) °C; dark		than 20%
Exposure time:	Minimum 2160 h		

Number of samples:	3 samples Black	Pass
	3 samples Grey	Pass



CTR 1204 January 4, 2023 Commscope.com

#### 6.3 Fungus resistance (Mold growth)

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	March 2016

Method and condition	ns	Test method followed	Requirements
Method and condition  Strains:  Inoculation conditions: Temperature: Relative humidity: Time:	2 mixed spore suspensions according to ISO846 and ASTM G21  Test severity 1 (29 ± 1) °C ≥ 90% RH 28 days		Visual examination (see 2.3) When a rating 0 is obtained, the material is considered fungus resistant and no further testing is required. When a rating of 1 or 2 is obtained, the effect of mould growth shall be evaluated by measuring a representative performance property (e.g. tensile strength at yield and elongation at yield for thermoplastic polymers, a compression set, a Shore A hardness for elastic materials, or any other test which checks a
			relevant property) both before and after exposure of the material samples. The average change in mechanical characteristics of the tested material samples shall be less than 20 %.  A rating of more than 2 is not allowed.

Number of samples:	4 samples Black	Pass
	4 samples Grey	Pass

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 7 Detailed test results for storage and transport performance

#### **7.1 Cold**

#### General

Product	NOVUX™ SEC 100 aerial wall terminal	
Date of testing	November 2022	

Method and conditi	ons	Test method followed	Requirements
Temperature: Duration:	(-40 ± 2) °C 96 h	IEC 61300-2-17	Visual examination (see 2.3) No defects which would adversely affect product performance or functionality after installation

#### Results

Number of camples:	Λ	Dace
Number of samples:	4	Pass

#### 7.2 Dry heat

#### General

Product	NOVUX™ SEC 100 aerial wall terminal
Date of testing	November 2022

Method and conditions		Test method followed	Requirements
Temperature: Humidity: Duration:	(+70 ± 2) °C Uncontrolled 96 h	IEC 61300-2-18	Visual examination (see 2.3) No defects which would adversely affect product performance or functionality after installation

Number of samples:	4	Pass
--------------------	---	------



CTR 1204 January 4, 2023 Commscope.com

#### 7.3 Damp heat (steady state)

#### General

Product	NOVUX <sup>™</sup> SEC 100 aerial wall terminal
Date of testing	November 2022

Method and conditions		Test method followed	Requirements
Temperature: Humidity: Duration:	(+40 ± 2) °C (+93 ± 3) % RH 96 h	IEC 61300-2-19	Visual examination (See 2.3) No defects which would adversely affect product performance or functionality after installation

Number of samples:	4	Pass





CTR 1204 January 4, 2023 Commscope.com

#### 8 Test sample description

#### 8.1 Sealing performance test samples

#### **Photo of samples**



#### **Used cables in the test samples:**

Location	PRD Requirements	Cable data sheet file name ULIMS folder	Cable name / info Cable description / dimensions	Strength member dia(mm)	Aramid	Cable type	Fiber type
5A2		<u>Datasheet cables\CDS-</u> 1301 Ø7.pdf	Draka Ø 7		No	Loose tube single fiber	G652D
20A3		Datasheet cables\P03317AMA Ø6.pdf	760239869 Ø 6	Ø1.5	Yes	Loose tube single fiber	G657A1
22A2		Datasheet cables\ET2558-10.0- CABO OPTICO CFOA- AS80 - COMPACTO (2) Ø 8.pdf	Furukawa Ø8.2		Yes	Loose tube single fiber	G652D
21A1		Datasheet cables\UND1533 Distribution Conduite 02 à 288 Fo Ø 12.pdf	Acome Ø 12		No	Loose tube single fiber	G652D
Lab		Datasheet cables\CTO134_RICO2F Ø 3.pdf	Tratos Ø 3		Yes	Loose tube single fiber	G657A2





CTR 1204 January 4, 2023 Commscope.com

#### 8.2 Optical performance test samples

Property	Sample – Splice variant	Sample – Patch variant		
Sample ID.	1, 3	2, 4		
Description	Facade closure Splice panel SEC100 (high cover – 3 splice tray).	Facade closure Patch panel SEC100 (low cover – 1 splice tray) with 4pcs of the SC adapter in patch panel.		
MID	760254487	760254488 (for grey color)		
Splitter	-	NOVUX- SP- 104NNSOSE 860658246 711617400864		
Adapter type	-	SCA, LCA		
	<b>Drop cable</b> - Dual Jacket - COMMSCOPE GB 760241223 HW 26/02/2019 L1084 1F0 G657-A2 Ohc FRC ORANGE 2113 M			
Used Cable	Feeder cable 48F: COMMSCOPE GB F.0 CABLE 760239868 48x9/125 G5657A1 ULSZH			
	Feeder cable 24F: COMMSCOPE RECTRACTABLE FACADE 24 F G657A1 LSZH			

#### **Photos of samples**

#### Sample High-cover Splice-Black












CTR 1204 January 4, 2023 Commscope.com

#### Sample High-cover Splice-Grey






Sample Low-cover Patch-Black





#### **Optical test sample configuration**







CTR 1204 January 4, 2023 Commscope.com

#### 9 Test set-ups

#### 9.1 Sealing performance testing

Protection against ingress of dust IP5x



Protection against ingress of water IP5x



Assembly/ disassembly



Cable retention





CTR 1204 January 4, 2023 Commscope.com

#### Cable bending



#### Cable torsion



#### Impact







CTR 1204 January 4, 2023 Commscope.com

#### Change of temperature



#### Salt mist




#### 9.2 Optical performance testing

#### Test set-up retention



#### Optical part






CTR 1204 January 4, 2023 Commscope.com

#### Test set-up bending

Mechanical part



#### Optical part




#### Test set-up torsion

Mechanical part



#### Optical part






CTR 1204 January 4, 2023 Commscope.com


#### Test set-up Reconfiguration 1&2

#### Mechanical part






#### Optical part




#### Test set-up vibration & shock

#### Mechanical part



#### Optical part





CTR 1204 January 4, 2023 Commscope.com


#### Test set-up change of temperature

Environmental part





#### Optical part



#### 9.3 Storage and transport test set up

Test set-up Cold





CTR 1204 January 4, 2023 Commscope.com

#### Test set-up Dry heat



Test set-up damp heat (steady state)





CTR 1204 January 4, 2023 Commscope.com

### 10 Equipment and calibration

All equipment used for the testing was within calibration period. Detailed information can be provided on request.

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 11 Trade-marks

All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability, with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

Further information regarding CommScope's commitment can be found at www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability.

### **Customer Test Report**

CTR 1204 January 4, 2023 Commscope.com

#### 12 Contact information

Visit our website or contact your local CommScope representative for more information.

FIST and all trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services.

For technical assistance, customer service, or to report any missing/damaged parts, visit us at: <a href="http://www.commscope.com/SupportCenter">http://www.commscope.com/SupportCenter</a>

This product is covered by one or more U.S. patents or their foreign equivalents. For patents, see <a href="https://www.commscope.com/ProductPatent/ProductPatent.aspx">www.commscope.com/ProductPatent/ProductPatent.aspx</a>